



## Merlin point-of-use Reverse Osmosis System

# The biggest innovation in home RO technology in 30 years!

We've done it again. GE Infrastructure Water & and Process Technologies has achieved a revolutionary breakthrough in the water treatment industry. Out-of-the-box thinking and years of research have produced a totally new point-of-use drinking water system.

The new Merlin RO System features continuous-flow water production, so a storage tank is no longer required. The unit operates on line pressure, which eliminates the need for an electrical pump in most applications. The patented high-production, low-energy membrane reduces impurities in up to 720 gallons (2,725 liters)\* of water per day! This high-capacity performance creates new opportunities for commercial applications – at the price of a residential system.

Big innovation, bigger opportunities.

#### Like no other system!

- Continuous flow no storage tank necessary
- Uses line pressure only (>40 psi/2.76 bar)
- 1/2 gpm (1.89 lpm) permeate rate @50 psi (3.44 bar) + 77°F (25°C)
- Requires no pump, no electricity (>40 psi/2.76 bar)
- Compact design fits easily under sink
- Water Quality Association Gold Seal NSF/ANSI 58 Certified
- Consistent membrane efficiency
- Complete product literature and training support
- Consistent high recovery system means less water going to drain
- Multiple dispensing locations off one system

\*At 50 psi (3.44 bar), 77°F (25°C)



TOUGH STUFF High-durability Noryl® and polypropylene plastic construction provide years of dependable service

ALL THE RIGHT CONNECTIONS

Engineered for the fewest number of connection points – less chance of leaks

NO TANKS!

Loss of tank pressure and contamination worries are eliminated

SLEEK, GOOD LOOKS

Contemporary, appliance-style design creates consumer appeal

**NEVER RUNS DRY** 

Continuous permeate water flows at 1/2 gpm (1.89 lpm)

Tested and Certified by the Water Quality Association according to NSF/ANSI 58





IT'S A SNAP
Quick-latch snaps
into place and locks
down all four tubing
connectors in one
easy step

s OF IN cks Custo comp e made

STEADY STREAM
OF INCOME
Custom replacement
components will be
made available only
through professional

channels



BUILT-IN CONVENIENCE System's support leg also serves as a handy sump wrench

3 4

AT YOUR SERVICE Custom high-flow faucet (with air gap) developed specifically for this system



FITS IN NICELY Stand-alone compact profile takes up less space than other bulky systems



## A world of possibilities

Safe, clean water is in the news and on the minds of today's consumers. The Merlin Reverse Osmosis System addresses those concerns. Water treatment professionals will now have a truly innovative product that opens doors and provides homeowners with effective, economical solutions.

The commercial market also presents unique opportunities for growth. The Merlin RO System is fully capable of serving a variety of applications such as restaurants, pubs, water coolers, ice-makers, aquariums and more – all at a price point well below current commercial systems.



#### How does your current system compare?

	Merlin RO	Standard RO
Average Daily Production Rate*	720 gpd	10-50 gpd
Water Storage Tank	None needed	Integral part of system
Install Time	1 Hour	Up to 4 Hours*
Designed for Use with Refrigerator Ice Makers	Yes	No
System Efficiency**	25-33%	As little as 5%
Dispensing Locations	2+	1-2

<sup>\*</sup>Based on inlet conditions of 50 psi (3.44 bar), 77°F (25°C).

#### Performance Specifications<sup>†\*</sup>

Specification	Minimum	Maximum	Average
Permeate Flow Rate**	0.33 Gallons/Minute (1.25 Liters/Minute)	0.75 Gallons/Minute (2.84 Liters/Minute)	0.50 Gallons/Minute (1.89 Liters/Minute)
TDS Rejection (NaCI)**	90%	99%	93%

<sup>&</sup>lt;sup>†</sup>Based on 50 psi (3.44 bar), 77°F (25°C), 750 mg/L NaCl, 25% recovery.

<sup>\*\*</sup>Efficiency rating is identical to recovery rating when the system is tested without a storage tank or when a storage tank is bypassed.

<sup>\*</sup>Specifications based on GE Osmonics internal test data.

<sup>\*\*</sup>For complete WQA test results to NSF/ANSI 58 Standard, see Merlin product data sheet P/N 1263717.

#### **Minimum and Maximum Operating Conditions**

Condition*	Minimum	Maximum
Inlet Pressure	40 psi (2.76 bar)	80 psi (5.52 bar)
Inlet Temperature	40°F (4.44°C)	100°F (37.78°C)
Inlet TDS	50 mg/L	2,000 mg/L
Inlet Hardness	0 mg/L - (0 grain)	171 mg/L - (10 grain)
Inlet Chlorine	0 mg/L	1.0 mg/L
Inlet Iron	0 mg/L	.1 mg/L
Inlet Manganese	0 mg/L	.05 mg/L

<sup>\*</sup>System is designed for use on potable water sources only.

#### **Tubing/Fitting Dimensions**

**Inlet Tubing** 

→ 4 feet of 1/2" natural tubing (1.22 meters of 12.7 mm natural tubing)

**Concentrate Tubing** 

→ 4 feet of 3/8" black tubing

(1.22 meters of 9.53 mm black tubing)

**Permeate Tubing** 

→ 4 feet of 3/8" blue tubing

(1.22 meters of 9.53 mm blue tubing)

**Drain Tubing** (for airgap installation)

→ 3 feet of 1/2" red tubing (0.91 meters of 12.7 mm red tubing)

Drain Connection

→ 3/8" or 1/2"
(9.53 mm or 12.7 mm)

**Carbon Post Filter** 

→ 3/8" quick disconnect fittings (9.53 mm quick disconnect fittings)

#### **Inlet Connectors**

Option 1

→ 3/8" x 3/8" x 1/2" tee (9.53 mm x 9.53 mm x 12.7 mm tee)

Option 2

→ 1/2" x 1/2" x 1/2" tee (12.7 mm x 12.7 mm x 12.7 mm tee)

Option 3

→ 14 mm x 14 mm x 12.7 mm tee

Option 4

→ 15 mm x 15 mm x 12.7 mm tee



#### **Filter/Membrane Performance Specifications**

Filter	Dime	ensions	Flow	Average
Туре	Length	Diameter	Rate*	Life
Carbon Prefilter	17.0"	2.9"	3.75 GPM	6 months (5,000 gal)
	(43.2 cm)	(7.4 cm)	(14.2 LPM)	(18,925 liters)
RO Element	18.75"	3.16"	0.25 GPM	2-4 years
	(47.6 cm)	(8.0 cm)	(0.95 LPM)	
Carbon Postfilter	10.5"	2.6"	.750 GPM	6 months
	(26.7 cm)	(6.6 cm)	(2.8 LPM)	

<sup>\*</sup>Based on: 50 psi (3.44 bar), 55°F (25°C), 750 mg/L NaCI, 25% Recovery, 1.0 mg/L inlet chlorine

### **Options**


Booster Pump → For low pressure applications


Membrane Rinse System → Permeate flushing accumulator

Ice Maker Installation Kit → Connections to 1/4" ice maker line

10-micron Sediment Prefilter ightharpoonup For commercial applications and non-chlorinated water supplies


#### Outline Dimensions - Inches (cm)





# Estimated System Flow Rate (GPM) Temperature vs. Pressure @750ppm NaCI/RO

#### Pressure (bar)\*



\*Pressure measured at membrane element inlet

Flow Adjustment Based on TDS Estimated Flow Change from 750ppm NaCl/RO = -0.0002 (TDS) + 0.15



North American Sales 5730 N. Glen Park Road Milwaukee, WI 53209-4403 USA (262) 238-4400 Phone

(262) 238-4402 Fax

Euro/Africa Operations 230 rue Robert Schuman ZA des Uselles

F-77350 Le Mée sur Seine FRANCE +33 1 64 10 2000 Phone

+33 1 64 10 3747 Fax

Asia/Pacific Operations 1044/8 SOI 44/2 Sukhumvit Road Parkanog Bangkok 10110 THAILAND +66 2 38 14213 Phone +66 2 39 18183 Fax For More Information: Call GE Infrastructure Water & Process Technologies; Household Water Group at (262) 238-4400 or (800) 279-9404, or visit www.qewater.com

This system has been tested according to NSF/ANSI 58 for reduction of substances listed below. The concentration of the indicated substances in water entering the system was reduced to a concentration less than or equal to the permissible limit for water leaving the system, as specified in NSF/ANSI 58. The substances are: Arsenic, Barium, Cadmium, Chromium (Hexavalent), Chromium (Trivalent), Copper, Fluoride, Lead, Nitrate, Nitrite, Radium 226/228, Selenium and TDS.







